## Micro X-II Autoclavable



The Micro X-II Autoclavable version is specially designed to withstand the rigors of sterile processing, and OR workflows which involves repeated of autoclave and chemical cleaning cycles.





Extreme durability and reliability







- OR Trays
- · Healthcare Equipments Management
- Assets Tracking in Autoclavable Environment

LEARN MORE >


Performance Characteristics		
Read range (handheld) <sup>1</sup>	Up to 22 ft (7 m)	
Read range (fixed) <sup>1</sup>	Up to 32 ft (10 m)	
Polarization	Linear	
Mounting system	Screws (Rivet hole, M3) Pop rivets (Max size 3.0mm) Adhesive (optional)	

1. Performance based on standard testing methodologies. Performance may vary depending on environmental factors and reader output power.

Functional Specifications		
RF protocol	EPC global Class 1 Gen2	
Frequency	902-928 (US); 865-868 (EU)	
IC type (chip)1	Alien Higgs-3	
Memory	96-EPC bits, 64-bit unique TID, 512 -bit user memory	
Material	High-performance engineered polymer	

1. The chip data retention is up to 50 years, based on chip operating under general environment conditions.

# Radiation Pattern





Environmental Specifications		
Operational temperature	-40°C to +85°C	
Survival temperature	-40°C to +150°C	
Peak temperature	+200°C	
Chemical resistance	Various caustic chemicals <sup>1</sup>	
IP rating	IP69K	
Compression strength	181 psi (1250 kPa)	
Shock (drop)	3 ft (1 m) to concrete/granite	
Vibration	MIL-STD-810G	

 The chemical resistance is based on the concentration of solutions and application environment. Please contact Xerafy for further details on chemical resistance.


Industry Compliance		
RoHS	EU Directive 2011/65/EU	
CE	Yes	
ATEX/IECEx	Compliant	
Warranty	1 year	

Order Information		
X1130-US140-H3	Micro X-II Autoclavable US	
X1130-EU140-H3	Micro X-II Autoclavable EU	
Optional service	Encoding / Laser etching	



# **Product Dimensions and Weight**


Dimensions (in)	2.01 x 1.43 x 0.30
Tolerance	+/- 0.02
Dimensions (mm)	51 x 36.3 x 7.5
Tolerance	+/- 0.5
Weight	0.92 oz (26 g)




### **Installation Instructions**









Instructions for optimal performances:

- 1. Drill two holes on the subject metal surface. (ø 4mm, picth: 45.7 mm)
- 2. Insert two  $\phi 3.0 mm$  (recommended size) rivets on the tag.
- 3. Fix the tag on the metal surface with a rivet gun.
- \* Can also be attached via adhesive / epoxy.

#### **About Xerafy**

Xerafy designs and manufactures the world's toughest RFID tags to power Industrial IoT applications in Aerospace, Oil & Gas, Automotive, Healthcare and Manufacturing.

For Product inquiries: <a href="mailto:sales@xerafy.com">sales@xerafy.com</a> Singapore | China | US | UK

GO TO WEBSITE >